

# Square Shims

For Motor Base / For Pillow Block

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

# Square Shim Package / Square Shims (Adjustment)

For Motor Base / For Pillow Block

RoHS10

Type		Material	Hardness	Thickness (T) Tolerance				
For Motor Base	For Pillow Block			0.05	0.1	0.2	0.5	1.0
CIMMS	CIMSS	SUS304H	370-430HV	±0.005	±0.02	±0.03	±0.04	±0.05
CIMMB	CIMSB	Brass (C2801P or C2680P)	-	±0.005	±0.02	±0.03	±0.05	±0.08
CIMM	CIMSN	SPCC Equivalent	-	-	±0.03	±0.03	±0.06	±0.11

Part Number		T Selection	A	C	Q	Unit Price													
Type	No.					CIMMS			CIMMB			CIMM							
				T0.05	T0.1	T0.2	T0.5	T1.0	T0.05	T0.1	T0.2	T0.5	T1.0	T0.1	T0.2	T0.5	T1.0		
CIMMS CIMMB CIMM	1035	(0.05) For CIMMB and CIMMS only	10	5	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	
	1245		12	6	4.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	1455		14	7	5.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	1665		16	8	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	2009		20	10	9	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	3013		30	15	13	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	4312		43	22	12	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	4814		48	24	14	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	5314		53	27	14	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	6816		68	34	16	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	8320		83	42	20	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	9825		98	49	25	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	11830		118	54	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	20036		200	100	36	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Part Number		T Selection	A	B	C	Q	D	E	Applicable Pillow Block	Unit Price								
Type	No.									CIMSS			CIMSB			CIMSN		
				T0.05	T0.1	T0.2	T0.5	T1.0	T0.05	T0.1	T0.2	T0.5	T1.0	T0.1	T0.2	T0.5	T1.0	
CIMSS CIMSB CIMSN	10	(0.05) For CIMSS and CIMSB only	16	17.5	10.5	7	7	2	PBT10, PBR10, PBR10	-	-	-	-	-	-	-	-	-
	12		16	18	10.5	7	7	2.5	PBT12, PBR12, PBR12	-	-	-	-	-	-	-	-	-
	15		16	20	11.5	7	7	2.5	PBT15, PBR15, PBR15	-	-	-	-	-	-	-	-	-
	17		18	21	12	7	8	2.5	PBT17, PBR17, PBR17	-	-	-	-	-	-	-	-	-
	20		20	24.5	14.5	10	10	3	PBT20, PBR20, PBR20	-	-	-	-	-	-	-	-	-
	25		20	27.5	16.5	10	10	3	PBT25, PBR25, PBR25	-	-	-	-	-	-	-	-	-
	30		26	33	20	13	13	4	PBT30, PBR30, PBR30	-	-	-	-	-	-	-	-	-
	204A		40	27	15	13	-	-	UCPA204 UCUP204	-	-	-	-	-	-	-	-	-
	205A		45	30	16	13	-	-	UCPA205 UCUP205	-	-	-	-	-	-	-	-	-
	206A		50	36	22	17	-	-	UCPA206 UCUP206	-	-	-	-	-	-	-	-	-
	207A		55	41	26	17	-	-	UCPA207 UCUP207	-	-	-	-	-	-	-	-	-
	208A		58	41	25	17	-	-	UCPA208 UCUP208	-	-	-	-	-	-	-	-	-
	204		38	42	26	13	-	-	UCP-204	-	-	-	-	-	-	-	-	-
	205		38	42	25	13	-	-	UCP-205	-	-	-	-	-	-	-	-	-
	206		48	54	32	17	-	-	UCP-206	-	-	-	-	-	-	-	-	-
207	48	54	34	17	-	-	UCP-207	-	-	-	-	-	-	-	-	-		
208	54	58	35	17	-	-	UCP-208	-	-	-	-	-	-	-	-	-		
209	54	60	38	17	-	-	UCP-209	-	-	-	-	-	-	-	-	-		
210	60	65	42	20	-	-	UCP-210	-	-	-	-	-	-	-	-	-		

Ordering Example: Part Number - T  
CIMM2009 - 0.5  
CIMSN204A - 0.1

RoHS10

Type		Material	Hardness	Thickness (T) Tolerance				
For Motor Base	For Pillow Block			0.05	0.1	0.2	0.5	1.0
PACK-CIMMS	PACK-CIMSS	SUS304H	370-430HV	±0.005	±0.02	±0.03	±0.04	±0.05

Part Number		T Selection	A	B	C	Q	D	E	Unit Price											
Type	No.								T0.05	T0.1	T0.2	T0.5	T1.0							
For Motor Base (SUS304H) PACK-CIMMS	1035	0.05	10	-	5	3.5	-	-	-	-	-	-	-	-	-	-	-	-		
	1245		12	-	6	4.5	-	-	-	-	-	-	-	-	-	-	-	-	-	
	1455		14	-	7	5.5	-	-	-	-	-	-	-	-	-	-	-	-	-	
	1665		16	-	8	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	
	2009		20	-	10	9	-	-	-	-	-	-	-	-	-	-	-	-	-	
	3013		30	-	15	13	-	-	-	-	-	-	-	-	-	-	-	-	-	
	4312		43	-	22	12	-	-	-	-	-	-	-	-	-	-	-	-	-	
	4814		48	-	24	14	-	-	-	-	-	-	-	-	-	-	-	-	-	
	5314		53	-	27	14	-	-	-	-	-	-	-	-	-	-	-	-	-	
	6816		68	-	34	16	-	-	-	-	-	-	-	-	-	-	-	-	-	
	8320		83	-	42	20	-	-	-	-	-	-	-	-	-	-	-	-	-	
	9825		98	-	49	25	-	-	-	-	-	-	-	-	-	-	-	-	-	
	For Pillow Block (SUS304H) PACK-CIMSS		10	0.1 0.2 0.5 1.0	16	17.5	10.5	7	7	2	-	-	-	-	-	-	-	-	-	-
			12		16	18	10.5	7	7	2.5	-	-	-	-	-	-	-	-	-	-
			15		16	20	11.5	7	7	2.5	-	-	-	-	-	-	-	-	-	-
17		18	21		12	7	8	2.5	-	-	-	-	-	-	-	-	-	-		
20		20	24.5		14.5	10	10	3	-	-	-	-	-	-	-	-	-	-		
25		20	27.5		16.5	10	10	3	-	-	-	-	-	-	-	-	-	-		
30		26	33		20	13	13	4	-	-	-	-	-	-	-	-	-	-		
204A		40	27		15	13	-	-	-	-	-	-	-	-	-	-	-	-	-	
205A		45	30		16	13	-	-	-	-	-	-	-	-	-	-	-	-	-	
206A		50	36		22	17	-	-	-	-	-	-	-	-	-	-	-	-	-	
207A		55	41		26	17	-	-	-	-	-	-	-	-	-	-	-	-	-	
208A		58	41		25	17	-	-	-	-	-	-	-	-	-	-	-	-	-	
204		38	42		26	13	-	-	-	-	-	-	-	-	-	-	-	-	-	
205		38	42		25	13	-	-	-	-	-	-	-	-	-	-	-	-	-	
206		48	54		32	17	-	-	-	-	-	-	-	-	-	-	-	-	-	
207	48	54	34	17	-	-	-	-	-	-	-	-	-	-	-	-	-			
208	54	58	35	17	-	-	-	-	-	-	-	-	-	-	-	-	-			
209	54	60	38	17	-	-	-	-	-	-	-	-	-	-	-	-	-			
210	60	65	42	20	-	-	-	-	-	-	-	-	-	-	-	-	-			

Ordering Example: Part Number - T  
PACK-CIMMS2009 - 0.5  
PACK-CIMSS204A - 0.1  
Please specify number of packages to order.  
Quantity 1 means one package.

RoHS10

Type		Material	Surface Treatment	Hardness	Thickness (T) Tolerance	
One Slot	Two Slots				0.5	1.0
ASA	ASF	SPCC Equivalent	Black Oxide	-	±0.05	±0.1
ASAS	-	SUS304H	-	370-430HV	±0.05	±0.1

Part Number		No.	A	C	Q	ASA		ASAS		Part Number	T	P	L	Unit Price	Volume Discount Rate
Type	T					T0.5	T1.0	T0.5	T1.0						
				Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate					1 - 49 pc(s)	50 - 100
ASA ASAS	0.5 1.0	1035	10	5	3.5	-	-	-	-	ASF	0.5	30	50	-	-
		1245	12	6	4.5	-	-	-	-					40	60
		1455	14	7	5.5	-	-	-	-					50	70
		1665	16	8	6.5	-	-	-	-					30	50
		2009	20	10	9	-	-	-	-					40	60

For orders larger than indicated quantity, please check with WOS.

Ordering Example: Part Number - No.  
ASA0.5 - 1035  
Part Number - P  
ASF0.5 - 30