

Harness Part Material AC Servo Motor Compatible Harnesses

Series Name	Harness Type	Model	Connector 1 Part Number	Related Components	Connector 2 Part Number	Related Components	Crimp Terminal Used	A (C) Cable Part Number	B (D) Cable Part Number	
SV	Power Supply OP.2079	SVPK-SV1	-	-	J17-06FMH-7KL-1M-CF (Not available)	SJ1F-01GF-P0.8	RB01 25-4RE	NA3CT-20-4 (O4711)	NA3CTR-22-4 (O4712)	
		SVPK-SV2	-	-	J27-06FMH-7KL-1M-CF (Not available)	SJ2F-01GF-P1.0	RB01 25-4RE	NA3CT-20-4 (O4711)	NA3CTR-22-4 (O4712)	
		SVPK-SV3	-	-	J37-06FMH-8KL-1L-CF (Not available)	SJ3F-41GF-P1.8	RB01 25-4RE	NA3CTF-T (O4711)	NA3CTF-R (O4712)	
		SVPK-SV4	-	-	MMS3106B18-10S (O3219)	MMS3057-10A	-	NA3CT-2-4 (O4105)	NA3CT-2-4 (O4409)	
		SVPK-SV5	-	-	MMS3106B-18-10-S (O3219)	-	-	NA3CT-12-4 (O4711)	NA3CTR-12-4 (O4712)	
		SVPK-SV6	-	-	MMS3106B-22-22-S (O3219)	-	-	NA3CT-10-4 (O4711)	NA3CTR-10-4 (O4712)	
		SVPK-SV7	-	-	MMS3106B-22-22-S (O3219)	-	-	NA3CT-8-4 (O4711)	NA3CTR-8-4 (O4712)	
		SVPK-SV1B	-	-	J17-06FMH-7KL-1M-CF (Not available)	SJ1F-01GF-P0.8	RB01 25-4RE	NA3CT-20-6 (O4711)	NA3CTR-22-6 (O4712)	
		SVPK-SV2B	-	-	J27-06FMH-7KL-1M-CF (Not available)	SJ2F-01GF-P1.0	RB01 25-4RE	NA3CT-20-6 (O4711)	NA3CTR-22-6 (O4712)	
		SVPK-SV3B	-	-	J37-06FMH-8KL-1L-CF (Not available)	SJ3F-41GF-P1.8	RB01 25-4RE	NA3CTF-T (O4711)	NA3CTF-R (O4712)	
	SVPK-SV4B	-	-	CM10-SP2S-M-D (O3364)	CM10-422S(S2)DB-100	-	NA3VPB-B	-		
	Encoder OP.2080	SVEK-SV1	55100-0670 (Not available)	-	54346-0070 (Not available)	-	-	NA32276T8B-A (O4713)	NA32276R8B-C (O4713)	
		SVEY-SV2	55100-0670	-	CM10-SP10S-M-D (O3364)	CM10-422S(S2)DB-100	-	NA32276T8B-A (O4713)	NA32276R8B-C (O4713)	
	MW	Power Supply OP.2082	SVPK-MV1	-	RBV1.25-PR	17215B-1 (O3433)	171638-1 (171636-1) (O3433)	-	NA3VPR-A (O4714)	-
SVPK-MV1B			-	RBV1.25-PR	172157-1 (O3433)	170364-1 (170360-1) (O3433)	-	NA3VBR-A (O4714)	-	
	Encoder OP.2083	SVEK-MV1	55100-0670 (Not available)	-	172161-1 (O3433)	170363-1 (170359-1) (O3433)	-	NA3VSB-25-3P (O4714)	-	
MINAS AS	Power Supply OP.2086	SVPP-A51	A0.75-90Y (Bar terminal)	N1.25-M4 (Round terminal)	JN6F04S1	ST-TMH-S-C18-3500	-	NA3CT-20-4 (O4711)	NA3CTR-20-4 (O4712)	
		SVPP-A52	-	-	JLD4V-6A20-4SE-EB-R (O3320)	-	-	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)	
		SVPP-A53	-	-	JLD4V-6A22-22SE-EB-R (O3320)	-	-	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)	
		SVPP-A54	-	-	JLD4V-6A22-22SE-EB-R (O3320)	-	-	NA3CT-12-4 (O4711)	NA3CTR-12-4 (O4712)	
	For Brake OP.2086	SVPP-A51B	N1.25-M4 (Round terminal)	-	JN6F02S1MR	ST-TMH-S-C18-3500	-	NA3VC-19-2	NA3MF-19-2	
		SVPP-A52B	-	-	JLD4V-6A20-18SE-EB-R (O3320)	-	-	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)	
		SVPP-A53B	-	-	JLD4V-6A24-11SE-EB-R (O3320)	-	-	NA3CT-20-2 (O4203)	NA3UCR-20-2 (O4417)	
		SVPP-A54B	-	-	JLD4V-6A24-11SE-EB-R (O3320)	-	-	NA3CT-10-4 (O4711)	NA3CTR-10-4 (O4712)	
	For Encoder OP.2088	SVEP-A51	55100-0670 (Not available)	-	JN6F07S1M1 (Not available)	LY10-C1-A1-10000	-	NA32276T8B-C (O4713)	NA32276R8B-E (O4713)	
		SVEP-A52	55100-0670 (Not available)	-	JN2DS10S1-R (Not available)	-	-	NA3VCSB-25-3P (O4311)	NA3MFSB-25-3P (O4511)	
	MINAS A4	Motor OP.2091	SVPP-MIA41	-	-	JLD4V-6A20-4SE-EB-R (O3320)	JLD4-2022CK-14	N2-M4	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)
			SVPP-MIA41S	-	-	JLD4V-6A20-4SE-EB-R (O3320)	JLD4-2022CK-14	(Round) N2-M4 (Bar) A2.5-8BU	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)
			SVPP-MIA42	-	-	JLD4V-6A22-22SE-EB-R (O3320)	JLD4-2022CK-14	N5.5-S4	NA3CT-12-4 (O4711)	NA3CTR-12-4 (O4712)
			SVPP-MIA43S	-	-	JLD4V-6A20-18SE-EB-R (O3320)	JLD4-2022CK-14	(Round) N2-M4 (Bar) A2.5-8BU	NA3CT-14-4 (O4711)	NA3CTR-14-4 (O4712)
SVPP-MIA44			-	-	JLD4V-6A24-11SE-EB-R (O3320)	JLD4-2428CK-17	N5.5-S4	NA3CT-12-4 (O4711)	NA3CTR-12-4 (O4712)	
SVPP-MIA45S			-	-	17215B-1 (O3433)	170366-1	(Round) N1.25-M4 (Bar) A1.5-8BK	NA3CT-18-4 (O4711)	NA3CTR-18-4 (O4712)	
SVPP-MIA41B			-	-	JLD4V-6A20-18SE-EB-R (O3320)	JLD4-2022CK-14	(1.6AWG) N1.25-M4 (1.6AWG) N2-M4	NA3CT-14-4 (O4711) NA3UC-19-2 (O4203)	NA3CTR-14-4 (O4712) NA3UCR-19-2 (O4417)	
SVPP-MIA41BS			-	-	JLD4V-6A20-18SE-EB-R (O3320)	JLD4-2022CK-14	(1.6AWG) A2.5-8BU (1.6AWG) A2.5-8BU N2-M4	NA3CT-14-4 (O4711) NA3UC-19-2 (O4203)	NA3CTR-14-4 (O4712) NA3UCR-19-2 (O4417)	
SVPP-MIA42B			-	-	JLD4V-6A24-11SE-EB-R (O3320)	JLD4-2428CK-17	(1.6AWG) N1.25-M4 (1.6AWG) N2-M4	NA3CT-12-4 (O4711) NA3UC-19-2 (O4203)	NA3CTR-12-4 (O4712) NA3UCR-19-2 (O4417)	
SVPP-MIA43B			-	-	172157-1 (O3320)	170366-1	N1.25-M4	NA3UC-19-2 (O4203)	NA3UCR-19-2 (O4417)	
Encoder OP.2092		SVEP-MIA41	55100-0670 (Not available)	-	172160-1 (O3320)	170365-1	-	NA3VSB-25-3P (O4327)	NA3MFSB-25-3P (O4539)	
		SVEP-MIA42	55100-0670 (Not available)	-	MMS3106B-20-29-S (O3219)	MMS3057-12A	-	NA3VSB-25-3P (O4327)	NA3MFSB-25-3P (O4539)	

- Harness Selection Method
- PLC Compatible Harnesses
- Relay Terminal Compatible Harnesses
- Touch Panel Compatible Harnesses
- AC Servo Motor Compatible Harnesses
- Single-Axis Robot Compatible Harnesses
- Stepper Motor Compatible Harnesses
- RS-232C Harnesses
- I/O Board Compatible Harnesses
- Image Sensor Compatible Harnesses
- Sensor Compatible Harnesses