

[High Precision] Combination Stages

Features: Lightweight XYZ-Axis Cross Roller Stages made of aluminum alloy. Choose from combinations of XY-Axis profile heights and Z-axis stroke requirements.

■ Combination Stages



XYZPG



XYZLPG



XYZLSPG

Features: Combination Stages of Cross Roller as the base and Rotary/Goniometer Stages.

■ Combination Stages



①XYRPG
XY-Axis and Rotary Stage integrated P1991



③XYRSPG



②XYZLRPG



④XYZLRSRG

| Part Number | Stage Configuration | | | Stage Surface (mm) | External Dimension (mm) | Travel Distance (mm) | Load Capacity (N) | Weight (kg) | Unit Price |
|-------------|---------------------|-----------------|----------------|--------------------|-------------------------|----------------------|-------------------|-------------|------------|
| | Type | No. | Bottom | Top | | | | | |
| XYZPG | 40 | XYPG40 (P1943) | ZPG40 (P1968) | 40x40 | 84.5 77.5 173.5 | ±6.5 ±6.5 ±6.5 | 9.8 19.6 | 0.48 0.95 | |
| | 60 | XYPG60 (P1943) | ZPG60 (P1968) | 60x60 | 98.5 91.5 178.5 | ±6.5 ±6.5 ±6.5 | 19.6 39.2 | 0.95 1.12 | |
| | 80 | XYPG80 (P1943) | ZPG80 (P1968) | 80x80 | 149.5 135 236 | ±12.5 ±12.5 ±12.5 | 49.0 29.4 | 1.80 2.00 | |
| XYZLPG | 40 | XYPG40 (P1943) | ZLPG40 (P1973) | 40x40 | 96 77 80 | ±6.5 ±6.5 ±6.5 | 9.8 39.2 | 0.48 1.12 | |
| | 60 | XYPG60 (P1943) | ZLPG60 (P1973) | 60x60 | 116.5 91.5 95 | ±6.5 ±6.5 ±6.5 | 39.2 29.4 | 1.12 2.00 | |
| | 80 | XYPG80 (P1943) | ZLPG80 (P1973) | 80x80 | 150 135 95 | ±12.5 ±12.5 ±12.5 | 29.4 | 2.00 | |
| XYZLSPG | 40 | XYSPG40 (P1945) | ZLPG40 (P1973) | 40x40 | 98.5 80.5 62 | ±6.5 ±6.5 ±6.5 | 7.8 33.5 | 0.40 1.00 | |
| | 60 | XYSPG60 (P1945) | ZLPG60 (P1973) | 60x60 | 120.5 96.5 77 | ±6.5 ±6.5 ±6.5 | 23.5 29.4 | 1.00 1.70 | |
| | 80 | XYSPG80 (P1945) | ZLPG80 (P1973) | 80x80 | 151 126 77 | ±12.5 ±12.5 ±12.5 | 29.4 | 1.70 | |

For detailed dimensions, material and characteristics, see the CAD data and the catalog page for each stage.

For included screw sizes, see the pages for the bottom stages.

Knob Cover HDCVR13 (Sold Separately): Ø13 micrometer knob can be increased in diameter by installing the cover. P2004

Extension Cover HDEXT13 (Sold Separately): Ø13 micrometer head knob can be extended. P2004

Combinations of Cross Roller stages listed in this catalog.

| Part Number | Stage Configuration | | | Stage Surface (mm) | External Dimension (mm) | Travel Distance (mm) | Load Capacity (N) | Weight (kg) | Unit Price |
|--|---------------------|-----------------|----------------|--------------------|-------------------------|----------------------|--------------------|-------------|------------|
| | Type | No. | Bottom | Middle | Top | | | | |
| ①XYRPG (XY-Axis + Rotary) | 38 | XYPG40 (P1943) | RPG38 (P1982) | - | 038 84.5 81.5 60 | ±6.5 ±6.5 - | 9.8 Coarse 360° | 0.37 | |
| | 60 | XYPG60 (P1943) | RPG60 (P1982) | - | 060 98.5 95.5 65 | ±6.5 ±6.5 - | 29.4 Fine Feed ±5° | 0.78 | |
| | 85 | XYPG80 (P1943) | RPG80 (P1982) | - | 085 149.5 136 65 | ±12.5 ±12.5 - | 39.2 | 1.48 | |
| ②XYZLRPG (XY-Axis + Horizontal Surf. Z-Axis + Rotary) | 38 | XYPG40 (P1943) | ZLPG40 (P1973) | RPG38 (P1981) | 038 96 81.5 100 | ±6.5 ±6.5 ±3.0 | 8.9 Coarse 360° | 0.57 | |
| | 60 | XYPG60 (P1943) | ZLPG60 (P1973) | RPG60 (P1981) | 060 116.5 95.5 120 | ±6.5 ±6.5 ±5.0 | 29.4 Fine Feed ±5° | 1.40 | |
| | 85 | XYPG80 (P1943) | ZLPG80 (P1973) | RPG85 (P1981) | 085 149.5 136 120 | ±12.5 ±12.5 - | 24.7 | 2.48 | |
| ③XYRSPG (Low Profile XY-Axis + Rotary) | 38 | XYSPG40 (P1945) | RPG38 (P1982) | - | 038 98.5 82 42 | ±6.5 ±6.5 - | 8.8 Coarse 360° | 0.29 | |
| | 60 | XYSPG60 (P1945) | RPG60 (P1982) | - | 060 102.5 98 47 | ±6.5 ±6.5 - | 26.4 Fine Feed ±5° | 0.68 | |
| | 85 | XYSPG80 (P1945) | RPG80 (P1982) | - | 085 151 132 47 | ±12.5 ±12.5 - | 34.3 | 1.18 | |
| ④XYZLRSRG (Low Profile XY-Axis + Horizontal Surf. Z + Rotary) | 38 | XYSPG40 (P1945) | ZLPG40 (P1973) | RPG38 (P1981) | 038 98 82 82 | ±6.5 ±6.5 ±3.0 | 6.8 Coarse 360° | 0.49 | |
| | 60 | XYSPG60 (P1945) | ZLPG60 (P1973) | RPG60 (P1981) | 060 120.5 98 102 | ±6.5 ±6.5 ±5.0 | 20.6 Fine Feed ±5° | 1.28 | |
| | 85 | XYSPG80 (P1945) | ZLPG80 (P1973) | RPG85 (P1981) | 085 151 132 102 | ±12.5 ±12.5 - | 22.5 | 2.18 | |

For detailed dimensions, material and characteristics, see the CAD data and the catalog page for each stage.

For included screw sizes, see the pages for the bottom stages.

Knob Cover HDCVR13 (Sold Separately): Ø13 micrometer knob can be increased in diameter by installing the cover. P2004

Extension Cover HDEXT13 (Sold Separately): Ø13 micrometer head knob can be extended. P2004

Ordering Example
Part Number
XYRPG38

