

▼ Fuji Electric MICREX-SX Series Supported Cable Pin Assignment (Mark Tube Printing) Figure

NP1X3206-W NP1X3202-W	
GPN-FU2Y/GPN-FU2T (Note)	
(Custom No.) X-PLC0282	
B A	A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
CO, B	
CO, A	

FCN Male 40-Core
Product Page [▶578](#)

NP1X3206-A	
GPN-FU3Y/GPN-FU3T (Note)	
(Custom No.) X-PLC0283	
B A	A
PORT9 (1.8)	PORT21 (2.4)
PORT10 (1.9)	PORT22 (2.5)
PORT11 (1.10)	PORT23 (2.6)
PORT12 (1.11)	PORT24 (2.7)
PORT13 (1.12)	PORT25 (2.8)
PORT14 (1.13)	PORT26 (2.9)
PORT15 (1.14)	PORT27 (2.10)
PORT16 (1.15)	PORT28 (2.11)
PORT17 (2.0)	PORT29 (2.12)
PORT18 (2.1)	PORT30 (2.13)
PORT19 (2.2)	PORT31 (2.14)
PORT20 (2.3)	PORT32 (2.15)
CO, B4	CO, A4
CO, B3	CO, A3
PORT1 (1.0)	PORT5 (1.4)
CO, B2	CO, A2
PORT2 (1.1)	PORT6 (1.5)
PORT3 (1.2)	PORT7 (1.6)
CO, B1	CO, A1
PORT4 (1.3)	PORT8 (1.7)

FCN Male 40-Core
Product Page [▶578](#)

NP1X6406-W	
GPN-FU4Y/GPN-FU4T (Note)	GPN-FU5Y/GPN-FU5T (Note)
(Custom No.) X-PLC0284	(Custom No.) X-PLC0285
0/1 B A	2/3 B A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
CO, B	
CO, A	

FCN Male 40-Core
Product Page [▶578](#)

NP1Y32T09P1-A	
GPN-FU6Y/GPN-FU6T (Note)	
(Custom No.) X-PLC0286	
B A	A
PORT9 (12.8)	PORT21 (13.4)
PORT10 (12.9)	PORT22 (13.5)
PORT11 (12.10)	PORT23 (13.6)
PORT12 (12.11)	PORT24 (13.7)
PORT13 (12.12)	PORT25 (13.8)
PORT14 (12.13)	PORT26 (13.9)
PORT15 (12.14)	PORT27 (13.10)
PORT16 (12.15)	PORT28 (13.11)
PORT17 (13.0)	PORT29 (13.12)
PORT18 (13.1)	PORT30 (13.13)
PORT19 (13.2)	PORT31 (13.14)
PORT20 (13.3)	PORT32 (13.15)
P, B4	P, A4
P, B3	P, A3
PORT1 (12.0)	PORT5 (12.4)
M, B2	M, A2
PORT2 (12.1)	PORT6 (12.5)
PORT3 (12.2)	PORT7 (12.6)
M, B1	M, A1
PORT4 (12.3)	PORT8 (12.7)

FCN Male 40-Core
Product Page [▶578](#)

NP1Y32T09P1 NP1Y32U09P1	
GPN-FU7Y/GPN-FU7T (Note)	
(Custom No.) X-PLC0287	
B A	A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
PO, B	MO, B
PO, A	MO, A

FCN Male 40-Core
Product Page [▶578](#)

NP1Y64T09P1 NP1Y64U09P1	
GPN-FU8Y/GPN-FU8T (Note)	GPN-FU9Y/GPN-FU9T (Note)
(Custom No.) X-PLC0288	(Custom No.) X-PLC0289
0/1 B A	2/3 B A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
PO, B	MO, B
PO, A	MO, A

FCN Male 40-Core
Product Page [▶578](#)

NP1W3206T NP1W3206U	
GPN-FU10Y/GPN-FU10T (Note)	
(Custom No.) X-PLC0290	
B A	A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
CO	PO
	MO

FCN Male 40-Core
Product Page [▶578](#)

NP1F-HC2, NP1F-HC2MR NP1F-HC2MR1	
GPN-FU13Y/GPN-FU13T (Note)	
(Custom No.) X-PLC0293	
B A	A
B20	A20
B19	A19
B18	A18
B17	A17
B16	A16
B15	A15
B14	A14
B13	A13
B12	A12
B11	A11
B10	A10
B9	A9
B8	A8
B7	A7
B6	A6
B5	A5
B4	A4
B3	A3
B2	A2
B1	A1

FCN Male 40-Core
Product Page [▶578](#)

*Since the signal name of this item is complex, the mark tube is printed with connector pin numbers.

NP1W6406T NP1W6406U	
GPN-FU11Y/GPN-FU11T (Note)	GPN-FU12Y/GPN-FU12T (Note)
(Custom No.) X-PLC0291	(Custom No.) X-PLC0292
0/1 B A	2/3 B A
0.0 20 20	1.0
0.1 19 19	1.1
0.2 18 18	1.2
0.3 17 17	1.3
0.4 16 16	1.4
0.5 15 15	1.5
0.6 14 14	1.6
0.7 13 13	1.7
0.8 12 12	1.8
0.9 11 11	1.9
0.10 10 10	1.10
0.11 9 9	1.11
0.12 8 8	1.12
0.13 7 7	1.13
0.14 6 6	1.14
0.15 5 5	1.15
4 4	
3 3	
2 2	
CO, B	
CO, A	

FCN Male 40-Core
Product Page [▶578](#)

*When ordering, put the custom No. at the end of the model number. (See the product page for the model number)

*Be sure to confirm the signal name upon placing an order as it may slightly differ from the PLC manufacturer manual, in order to distinguish identical signal names.

Pins with no signal name are not connected. Cables are selected according to the number of required pins.

Model numbers marked with "A (Note)" are those of similar products sold in China. Please note that they are not sold in Japan.