

## Mitsubishi L Series Supported Cable Pin Assignment (Mark Tube Printing) Figure

L26CPU-BT [For L02CPU]	For LX41C4	For LX42C4		For LY41NT1P
<b>GNP-L28Y/GPN-L28T</b> (Custom No.) X-PLC0308	<b>GNP-L4Y/GPN-L4T</b> (Custom No.) X-PLC0001	<b>GNP-L5Y/GPN-L5T</b> (Custom No.) X-PLC0003	<b>GNP-L6Y/GPN-L6T</b> (Custom No.) X-PLC0004	<b>GNP-L7Y/GPN-L7T</b> (Custom No.) X-PLC0005
Input Connector 	Input Connector 	Input Connector 1 	Input Connector 2 	Output Connector 
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>

For LY42NT1P			
<b>GNP-L8Y/GPN-L8T</b> (Custom No.) X-PLC0008	<b>GNP-L9Y/GPN-L9T</b> (Custom No.) X-PLC0009		
Output Connector 1 	Output Connector 2 		
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>		

For LD75P4			
<b>GNP-L22Y/GPN-L22T</b> (Custom No.) X-PLC0018	<b>GNP-L23Y/GPN-L23T</b> (Custom No.) X-PLC0017		
Input / Output Connector 2 	Input / Output Connector 1 		
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>		

For LD75D4			
<b>GNP-L24Y/GPN-L24T</b> (Custom No.) X-PLC0022	<b>GNP-L25Y/GPN-L25T</b> (Custom No.) X-PLC0021		
Input / Output Connector 2 	Input / Output Connector 1 		
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>	<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>		

For LD62			
<b>GNP-L26Y/GPN-L26T</b> (Custom No.) X-PLC0027			
Input / Output Connector 			
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>			

For LD62D			
<b>GNP-L27Y/GPN-L27T</b> (Custom No.) X-PLC0028			
Input / Output Connector 			
<b>FCN Male 40-Core</b> <a href="#">Product Page</a> <span style="color: red;">▶546</span>			

\*When ordering, put the custom No. at the end of the model number. (See the product page for the model number)

\*Be sure to confirm the signal name upon placing an order as it may slightly differ from the PLC manufacturer manual, in order to distinguish identical signal names.

Pins with no signal name are not connected. Cables are selected according to the number of required pins.