


ミスミ

TiA₂N COATED SOLID CARBIDE DRILLS

TiA₂Nコート超硬ドリル

● ストレートシャンク / スタブ -STRAIGHT SHANK / STUB LENGTH-

TAC-SDB



S形シニング / スリレーキ / 直線切刃



● シャンク径 (d) は直径 (D) と同じです。

材質	超硬	TiA ₂ N
仕様	先端角 118°	スタブ
	23°~27°	再研磨

直径D、シャンク径d	公差 (h7)
1 ~ 3	0 -0.010
3.1 ~ 6	0 -0.012
6.1 ~ 8	0 -0.015

一般鋼 (SS-SC材)	合金鋼 (SCM)	調質鋼 (~45HRC)	高硬度鋼 (50HRC~)	工具鋼 (SKD, SKS)	ステンレス鋼 (SUS)	鋳鉄 (FC, FCD)	アルミ (Al)	銅 (Cu)	樹脂
◎	○	○		○		○	○	○	

◎=最適 ○=適

型番 TAC-SDB 1本単位

直径 D	溝長 l	全長 L	¥通常単価 30本以上はお見積り		
			1~4本	5~9本	10~29本
1	6	26	1,220	1,180	1,160
1.1	7	28	1,220	1,180	1,160
1.2	8	30	1,270	1,230	1,210
1.3	8	30	1,270	1,230	1,210
1.4	9	32	1,330	1,290	1,260
1.5	9	32	1,330	1,290	1,260
1.6	10	34	1,370	1,330	1,300
1.7	10	34	1,370	1,330	1,300
1.8	11	36	1,370	1,330	1,300
1.9	11	36	1,370	1,330	1,300
2	12	38	1,560	1,510	1,480
2.1	12	38	1,570	1,520	1,490
2.2	13	40	1,570	1,520	1,490
2.3	13	40	1,570	1,520	1,490
2.4	14	43	1,700	1,650	1,620
2.5	14	43	1,700	1,650	1,620
2.6	14	43	1,700	1,650	1,620
2.7	16	46	1,970	1,910	1,870
2.8	16	46	1,970	1,910	1,870
2.9	16	46	1,990	1,930	1,890
3	16	46	1,980	1,920	1,880
3.1	18	49	2,130	2,070	2,020
3.2	18	49	2,240	2,170	2,130
3.3	18	49	2,240	2,170	2,130
3.4	20	52	2,480	2,410	2,360
3.5	20	52	2,420	2,350	2,300
3.6	20	52	2,590	2,510	2,460
3.7	20	52	2,590	2,510	2,460
3.8	22	55	2,730	2,650	2,590
3.9	22	55	2,730	2,650	2,590
4	22	55	2,830	2,750	2,690
4.1	22	55	2,920	2,830	2,770

直径 D	溝長 l	全長 L	¥通常単価 30本以上はお見積り		
			1~4本	5~9本	10~29本
4.2	22	55	2,920	2,830	2,770
4.3	24	58	3,190	3,090	3,030
4.4	24	58	3,190	3,090	3,030
4.5	24	58	3,120	3,030	2,960
4.6	24	58	3,190	3,090	3,030
4.7	24	58	3,190	3,090	3,030
4.8	26	62	3,390	3,290	3,220
4.9	26	62	3,390	3,290	3,220
5	26	62	3,330	3,230	3,160
5.1	26	62	3,460	3,360	3,290
5.2	26	62	4,340	4,210	4,120
5.3	26	62	4,340	4,210	4,120
5.4	28	66	4,480	4,350	4,260
5.5	28	66	4,480	4,350	4,260
5.6	28	66	4,820	4,680	4,580
5.7	28	66	4,820	4,680	4,580
5.8	28	66	4,820	4,680	4,580
5.9	28	66	4,820	4,680	4,580
6	28	66	4,820	4,680	4,580
6.1	31	70	5,980	5,800	5,680
6.2	31	70	5,980	5,800	5,680
6.5	31	70	5,570	5,400	5,290
6.6	31	70	6,930	6,720	6,580
6.7	31	70	6,930	6,720	6,580
6.8	34	74	6,930	6,720	6,580
6.9	34	74	6,930	6,720	6,580
7	34	74	6,250	6,060	5,940
7.2	34	74	8,020	7,780	7,620
7.5	34	74	7,140	6,930	6,780
7.7	37	79	8,700	8,440	8,270
8	37	79	7,610	7,380	7,230

切削条件 P.762



Order 注文例

TAC-SDB 5

型番 直径(D)



Delivery 出荷日



在庫品

巻末-3

◎ご希望によりPM6:00迄、当日出荷受付致します。

5が特長!

- 汎用の超硬ドリルで幅広い用途に対応できます。
- TiA₂Nコートにより高速切削が対応可能です。