



# HEAT-RESISTANT ARM COVER / GLOVES FOR INJECTION / GLOVES FOR DIECASTING

shows in red

■ **Application** Use together with Gloves for Injection, the cover prevents exposure of the wrist / arm and sleeves from rolling up.

■ **Heat-Resistant Arm Cover (Cut-Resistant Arm Cover)**  
M-KAC



Total Length : Approx. 54 cm (before wearing)  
Quantity : 1 pair (left/right)

■ **Features**

- High-functioning arm cover made of Kevlar, with heat resistance of 260 degree as well as cut resistance (compliant with American National Standards Institute ANSI/ISEA105-2016 Cut Level A2).

| Part Number | Unit Price |
|-------------|------------|
| M-KAC       | Quotation  |



Order

Part Number

M-KAC



Days to Ship

Quotation



Price

Quotation

■ **Application** Use when handling operations with high temperature.

■ **Gloves for Injection (~230°C)**

M-HML



M Cloth material : Cotton  
Grip : Nitrile Rubber

■ **Gloves for Injection (~260°C)**

M-HMM




M Cloth material : Cotton / Kevlar  
Grip : Nitrile Rubber

■ **Gloves for Diecasting (~593°C)**

M-HMH



M Cloth material : Amorphous Silica Fiber  
Inner : Wool Cushion



M-HML: Use these gloves during the maintenance of screw, nozzle and band heater.

M-HMM: In addition to the above, these gloves are Kevlar blended, resulting in high function gloves with the same resistant properties as cut-resistant gloves.

M-HMH: These heat resistant gloves are for diecasting operation. Use them according to the temperature level.

| L   | A   | B   | C   | Part Number |      | Unit Price |
|-----|-----|-----|-----|-------------|------|------------|
|     |     |     |     | Type        | Size |            |
| 235 | 185 | 50  | 115 | M-HML       | S    | Quotation  |
| 265 | 210 | 55  | 115 | (~230°C)    | M    |            |
| 225 | 185 | 40  | 110 | M-HMM       | S    |            |
| 265 | 210 | 55  | 110 | (~260°C)    | M    |            |
| 270 | 210 | 60  | 140 | M-HMH       | S    |            |
| 350 | 220 | 130 | 155 | (~593°C)    | M    |            |
| 580 | 350 | 230 | 170 |             | L    |            |



Order

Part Number

M-HMM-S



Days to Ship

Quotation



Price

■ **Quantity Discount Rate**

| Order quantity | Standard service |     |     |       | Non-standard service - Large quantity |
|----------------|------------------|-----|-----|-------|---------------------------------------|
|                | 1                | 2~4 | 5~9 | 10~20 | 21~                                   |
| Rate           | Standard         | 5%  | 10% | 15%   | To be quoted                          |

Ⓞ For quantities not displayed here, refer to our MISUMI website for more information.